

❖ CM-140 MCL / CB-140 MCL Progressive Scan



- **Compact series 1/2" progressive scan camera**
- **Monochrome and Bayer mosaic color versions**
- **1380 (h) x 1040 (v) active pixels**
- **4.65 μm square pixels**
- **31 frames/second with full resolution in continuous operation**
- **30 frames/second with external trigger and full resolution**
- **Up to 74 frames/second with partial scan**
- **48 frames/second with vertical binning (CM-140 MCL only)**
- **Shutter speed from 32 μs to 2 sec. using Pulse Width Control**
- **Programmable exposure from 64 μs to 40 ms**
- **Pre-select and Pulse width trigger modes**
- **LVAL-synchronous/-asynchronous operation (auto-detect)**
- **Power over CL (PoCL) version available**
- **Auto iris lens video output allows a wider range of light**
- **10 or 8-bit output**
- **Setup by Windows NT/2000/XP via serial communication**




Specifications for CM-140 MCL / CB-140 MCL

Specifications	CM-140 MCL / CB-140 MCL																		
Sensor	1/2" progressive scan CCD																		
Pixel Clock	65 MHz																		
Frame rate full frame	31.08 frames/second (1052 lines per frame)																		
Active area	6.4 (h) x 4.8 (v) mm																		
Cell size	4.65 x 4.65 μm																		
Active pixels	1380 (h) x 1040 (v)																		
Color (CB-140 MCL)	Raw Bayer output, host-based interpolation																		
Read-out modes	<table border="0"> <tr> <td>Full</td> <td>1380 (h) x 1040 (v)</td> <td>31.08 fps</td> </tr> <tr> <td>1/2 partial scan</td> <td>1380 (h) x 520(v)</td> <td>46.57 fps</td> </tr> <tr> <td>1/4 partial scan</td> <td>1380 (h) x 269 (v)</td> <td>61.92 fps</td> </tr> <tr> <td>1/8 partial scan</td> <td>1380 (h) x 130 (v)</td> <td>73.97 fps</td> </tr> <tr> <td>2/3 partial scan</td> <td>1380 (h) x 694 (v)</td> <td>39.97 fps</td> </tr> <tr> <td>Vertical binning</td> <td>1380 (h) x 527 (v)</td> <td>48.86 fps*</td> </tr> </table> <p>*NOTE: CM-140 MCL only</p>	Full	1380 (h) x 1040 (v)	31.08 fps	1/2 partial scan	1380 (h) x 520(v)	46.57 fps	1/4 partial scan	1380 (h) x 269 (v)	61.92 fps	1/8 partial scan	1380 (h) x 130 (v)	73.97 fps	2/3 partial scan	1380 (h) x 694 (v)	39.97 fps	Vertical binning	1380 (h) x 527 (v)	48.86 fps*
Full	1380 (h) x 1040 (v)	31.08 fps																	
1/2 partial scan	1380 (h) x 520(v)	46.57 fps																	
1/4 partial scan	1380 (h) x 269 (v)	61.92 fps																	
1/8 partial scan	1380 (h) x 130 (v)	73.97 fps																	
2/3 partial scan	1380 (h) x 694 (v)	39.97 fps																	
Vertical binning	1380 (h) x 527 (v)	48.86 fps*																	
Sensitivity (CM-140 MCL)	0.3 Lux (On sensor, Max. gain, shutter off, 50% video)																		
Sensitivity (CB-140 MCL)	1.6 Lux (On sensor, Max. gain, shutter off, 50% video)																		
S/N ratio	>50dB (0 dB gain)																		
Video output	8 or 10 bit in Mini-CL																		
Auto-iris lens video	0.7 Vp-p																		
Gain	Manual, -3dB to +12dB																		
Synchronization	Int. X-tal or ext. trigger																		
Inputs	<table border="0"> <tr> <td>Camera Link</td> <td>Ext. trigger, LVDS (CC 1)</td> </tr> <tr> <td>TTL</td> <td>Ext. trigger 4V ±2V</td> </tr> </table>	Camera Link	Ext. trigger, LVDS (CC 1)	TTL	Ext. trigger 4V ±2V														
Camera Link	Ext. trigger, LVDS (CC 1)																		
TTL	Ext. trigger 4V ±2V																		
Outputs	<table border="0"> <tr> <td>Camera Link</td> <td>Clk., FVAL, LVAL, Data, EEN</td> </tr> <tr> <td>TTL</td> <td>XEEN</td> </tr> </table>	Camera Link	Clk., FVAL, LVAL, Data, EEN	TTL	XEEN														
Camera Link	Clk., FVAL, LVAL, Data, EEN																		
TTL	XEEN																		
Trigger modes	Pre-select, Pulse Width																		
Electronic shutter	<table border="0"> <tr> <td>Pre-set shutter</td> <td>1/31 to 1/10,000 in 10 steps</td> </tr> <tr> <td>Programmable exposure</td> <td>2L (64μs) to 1052L (40ms) in 1L steps</td> </tr> <tr> <td>Pulse Width Control</td> <td>32μs to 2 sec.</td> </tr> </table>	Pre-set shutter	1/31 to 1/10,000 in 10 steps	Programmable exposure	2L (64μs) to 1052L (40ms) in 1L steps	Pulse Width Control	32μs to 2 sec.												
Pre-set shutter	1/31 to 1/10,000 in 10 steps																		
Programmable exposure	2L (64μs) to 1052L (40ms) in 1L steps																		
Pulse Width Control	32μs to 2 sec.																		
Accumulation	Auto-detect LVAL-synchr. / asynchr.																		
Control interface	Mini-CL serial communication																		
Functions controlled by serial communication	Shutter, Trigger mode, Readout mode, Trigger Polarity, Black level, Gain,																		
Indicators on rear panel	LED for power and trigger input																		
Operating Temperature	-5°C to +45°C																		
Humidity (operation)	20 - 90% non-condensing																		
Storage temp./humidity	-25°C to +60°C / 20 to 90%																		
Vibration	10G (20Hz to 200 Hz XYZ)																		
Shock	70G																		
Regulations	CE (EN 61000-6-2, EN-61000-6-3), FCC part 15 class B, RoHS/WEEE																		
Power	12V DC ±10% 3 W																		
Lens mount	C-mount																		
Dimensions (H x W x L)	29 x 44 x 66 mm																		
Weight	115 g																		

Ordering Information

CM-140 MCL 1/2" Monochrome Progressive Scan Camera
 CB-140 MCL 1/2" Bayer Mosaic Color Progressive Scan Camera

FVAL auto-detect trigger function (next LVAL or immediate)



Connector pin-out

DC In / Trigger

HIROSE HR10A-10R-12PB-01

Pin 1	Ground
2	+12V DC
3	Ground
4	Auto Iris lens video output
5	Ground
6	N/C
7	N/C
8	Ground
9	XEEN out
10	Trigger in*
11	+12V DC
12	Ground

Mini-CL interface

Pin	Signal	Function
1 14	GND	-
2 15	+/-Tx0	CL Data
3 16	+/-Tx1	CL Data
4 17	+/-Tx2	CL Data
5 18	+/-Txclk	CL clk
6 19	+/-Tx3	CL Data
7 20	SerTC+/SerTC-	Serial in
8 21	SerTFG+/SerTFG-	Serial out
9 22	CC1-/CC1+	Ext. trig*
10 23	CC2+/CC2-	Not used
11 24	CC3-/CC3+	Not used
12 25	CC4+/CC4-	Not used
13 26	GND	-

For PoCL version pins 1 and 26 are used for +12V
 *) in Mini-CL or 12-pin Hirose

Dimensions


Front view

Side view


Bottom view

Rear view

Spectral Response CM-140 MCL



Spectral Response CB-140 MCL



Europe, Middle East & Africa
 Phone +45 4457 8888
 Fax +45 4491 8880

Asia Pacific
 Phone +81 45 440 0154
 Fax +81 45 440 0166

Americas
 Phone (Toll-Free) 1 800 445 5444
 Phone +1 408 383 0300



See the possibilities

Visit our web site on www.jai.com

Company and product names mentioned in this datasheet are trademarks or registered trademarks of their respective owners. IAI AS cannot be held responsible for any technical or typographical errors and reserves the right to make changes to products and documentation without prior notification.